

NELLCOR® OXiMAX® N-65™ HANDHELD PULSE OXIMETER

PERFORMANCE ON THE GO.

We added our latest technology to our most popular handheld oximeter to create the *OxiMax N-65™* handheld pulse oximeter. This portable oximeter is effective with a broad range of patients, standing up to difficult monitoring conditions such as low perfusion and signal interference, including motion, that can hamper other handhelds. Compatibility with our innovative *OxiMax* sensors, including the *MAX-FAST®* forehead sensor and *SoftCare™* nonadhesive sensor, further expands its versatility.

The small and lightweight *OxiMax N-65* handheld pulse oximeter is convenient for continuous monitoring or spot checks in physician offices or clinics, EMS/transport or in acute care settings. Its ergonomic shape and simple keypad make it easy to handle and operate. Wherever you need accurate, reliable SpO₂ measurements—count on the *OxiMax N-65* handheld pulse oximeter to meet the challenge.



CAPABLE AND CONVENIENT

- The *OxiMax N-65* offers accurate and reliable performance in monitoring conditions of low perfusion and signal interference.
- Compatible with complete line of *OxiMax* sensors.
- Audible and visible alarms.
- Bright blue, backlit display is easy to see, night or day.
- Long battery life: 19 or 40 hours depending on battery type.



OXIMAX SENSORS—A SMART CHOICE

Nellcor's extensive family of single-patient-use, reusable and specialty *OxiMax* sensors lets you make the best choice for each patient. For example, the *OxiMax MAX-FAST* forehead sensor is a more effective monitoring option than finger sensors during low perfusion because the forehead is not prone to vasoconstriction. The *MAX-FAST* sensor also offers an alternative when the hands are not accessible. *OxiMax SoftCare* nonadhesive sensors, which fit securely without adhesives, are a smart choice for patients with fragile skin, such as geriatric or burn patients.

PATIENT ASSESSMENT TOOL

Sensor Event Report* is a unique *OxiMax* feature that allows patient alarm events to be recorded within the *OxiMax* sensor while using the *OxiMax N-65* handheld pulse oximeter.

- As patients move to other areas of care, clinicians can view the alarm data from *OxiMax* standalone and multi-parameter monitors to quickly assess the frequency and severity of desaturation events.
- This feature is ideal for patients being transferred from EMS to hospital settings where *OxiMax* systems are used.

* This feature is only available in single-patient-use *OxiMax* sensors.

FEATURES AND SPECIFICATIONS

DESCRIPTION

The *OxiMax N-65* handheld pulse oximeter is intended for noninvasive continuous or spot check measurement of functional oxygen saturation of arterial hemoglobin (SpO₂). It can be used with adult, pediatric and neonatal patients and is compatible with the complete line of Nellcor *OxiMax* sensors. The monitor comes with four AA-size alkaline batteries and a reusable *OxiMax* sensor.

PERFORMANCE

Display Range

SpO₂: 0% – 100%
Pulse rate: 20 – 250 bpm

Accuracy

Saturation (% SpO₂: ± 1 SD):
Low perfusion: 70% to 100% ± 2 digits

Pulse rate:

Low perfusion: 20 to 250 bpm ± 3 digits

POWER

Requirements

6 V supplied by four AA-size batteries

Battery Life

Alkaline: 19 hours (typical)
Lithium: 40 hours (typical)

ENVIRONMENTAL

Storage/Shipping Temperature

-4°F to 158°F
(-20°C to 70°C)

Operating Temperature

41°F to 104°F
(5°C to 40°C)

Operating Altitude

-1,254 ft to 9,882 ft
(-382 m to 3,012 m)

Relative Humidity

15% to 95% noncondensing

PHYSICAL CHARACTERISTICS

Size

2.8 x 6.2 x 1.4 (inches)
(7.3 cm x 15.8 cm x 3.5 cm)

Weight (with batteries)

0.65 lb (0.29 kg)

Standards

EN60601-1-2: 2001 (CISPR 11, Class B)
EN60601-1: 1990 (A1+A2)
UL 60601-1, CAN/CSA C22.2 No. 601.1
(Class: Internally Powered, Type BF)
EN60601-1-8
EN865

Displays

Oxygen saturation, pulse rate, vertical bar graph

Indicators

Pulse amplitude, pulse search, low battery, alarm silence, interference, data in sensor, sensor disconnect, print

Optional Accessories

- Protective Boot (3 color options)
- Moisture-Resistant Jacket
- Carrying Case
- Citizen Portable Infrared Printer

Adult specifications are shown for the *OxiMax* MAX-A and MAX-N sensors with the *OxiMax N-65* pulse oximeter. Neonate specifications are shown for MAX-N sensors with the *OxiMax N-65* pulse oximeter. Saturation accuracy will vary by sensor type. Refer to Nellcor's Sensor Accuracy Grid Card for details. Refer to the *OxiMax N-65* operator's manual for complete description, instructions, warnings, cautions and specifications. Specifications are subject to change without notice.



tyco
Healthcare
Nellcor

4280 Hacienda Drive
Pleasanton, CA 94588
Tel 925.463.4000
Toll Free 1.800.635.5267
www.nellcor.com

Tyco Healthcare UK LTD.
154 Fareham Road
Gosport, UK PO13 0AS
Tel +44.1329.224000